



ABOUTBLU/ANATOMIC

SAFE KNIT

LE MANS BLACK YELLOW FLUO LOW

51376 24LA

TECH SOFT

S1PL FO SR ESD DGUV 112-191 EN ISO 20345:2022

UPPER	Breathable polyester jacquard f resistant. Anti-abrasion scuff-ca	fabric. Cut resistant, anti-fraying, rip and abrasion ap. Normal laces extra	
LINING	PLASMAFEEL Lining in 3D fabric that keeps the foot constantly cool and dry thanks to the instantaneous absorption of sweat and its immediate dispersion outside of the shoe. Breathable, antibacterial, resistant to wear and abrasion.		
INSOLE		Runproof, multi-layered, antistatic latex-foam fabric, that ad absorbent with anti-fungus activated carbons. Shock ch support.	SHOCK ABSORPTION IN THE HEEL
SOLE	ensures the maximum comformation Polyurethane outsole, with an	BASF PUR Elastopan ® polyurethane foam insole, ort and the absorption of the impact on all surfaces. elevated grip, resistant to wear, oils and hydrocarbons on the heel. It leaves no mark on the surface.	NO MARKING SOLE
LAST	ANATOMIC SOLE The anatomical shape of the injected sole, unlike removable insoles, is inalterable for the entire lifetime of the shoe. The Anatomic sole, following the natural morphology of the foot, provides a natural support to all its points, ensuring maximum comfort		
TOE CAP	POWER CAP is in multilayer fiberglass and rubber particulate. It stands out for its robustness and lightness, guaranteeing a shock absorption up to a max. 200 Joules. Being metal-free is is undetactable by a meta detector, and helps to maintain a constant body temperature. It provides maxmum safety even at extreme temperatures above and below zero, providing a thermal insulation that is better than aluminum or steel toe-caps. It is compliant with CSA Canada regulations and exceeds the EN-ISO12568 requirements.		METAL FREE
MIDSOLE	TEXON ENIGMA ZERO HT2 Non-metallic antistatic, flexible, anti-perforation fabric insole, built with several layers of high-tenacity fibres. It ensures perfect thermal insulation Compliant with: EN 12568:2012; EN ISO 20344/345; CSA-Z195-14; ASTM F2413-18		R. ANTHERS
ANTI-TORSION SUPPORT	COMPOSHANK Anti-torsion rigid ABS support. It is applied between the anti-perforation midsole and midsole, at the arch of the foot. It improves stability on stairs, where the support of the foot is not ideal		
	SILVER STRIP DISCHARGE (SSD) Conductive cotton tape with silver threads, positioned inside the upper and in direct contact with the foot. It is an extra Anti-static device, increasing and stabilizing the dispersive capacity throughout the life of the shoe.		QLASMA,
ANTI-STATIC DEVICE	• •		\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\